

# 全錫鋼被覆鑽頭

## TUNGSTEN CARBIDE COATED DRILL



### 適合材質：

一般鋼料、合金鋼、模具鋼、  
不鏽鋼、銅、鋁、鑄鐵。

### Applicable materials:

General steel, alloy steel, mold steel, stainless  
steel, copper, aluminum, cast iron.

| EDP No.   | Dø  | dø  | L <sub>2</sub> | L  | L <sub>4</sub> | L <sub>s</sub> |
|-----------|-----|-----|----------------|----|----------------|----------------|
| CCD- 4010 | 1.0 | 1.5 | 7              | 38 | 28             | 5              |
| CCD- 4011 | 1.1 |     |                |    |                |                |
| CCD- 4012 | 1.2 | 1.5 | 8              | 38 | 28             | 6              |
| CCD- 4013 | 1.3 |     |                |    |                |                |
| CCD- 4014 | 1.4 | 1.5 | 9              | 38 | 28             | 7              |
| CCD- 4015 | 1.5 |     |                |    |                |                |
| CCD- 4016 | 1.6 | 2   | 10             | 42 | 30             | 8              |
| CCD- 4017 | 1.7 | 2   | 12             | 42 | 30             | 9              |
| CCD- 4018 | 1.8 |     |                |    |                |                |
| CCD- 4019 | 1.9 |     |                |    |                |                |
| CCD- 4020 | 2.0 | 3   | 14             | 46 | 32             | 10             |
| CCD- 4021 | 2.1 |     |                |    |                |                |
| CCD- 4022 | 2.2 |     |                |    |                |                |
| CCD- 4023 | 2.3 |     |                |    |                |                |
| CCD- 4024 | 2.4 | 3   | 18             | 52 | 32             | 13             |
| CCD- 4025 | 2.5 |     |                |    |                |                |
| CCD- 4026 | 2.6 |     |                |    |                |                |
| CCD- 4027 | 2.7 |     |                |    |                |                |
| CCD- 4028 | 2.8 | 4   | 20             | 56 | 34             | 15             |
| CCD- 4029 | 2.9 |     |                |    |                |                |
| CCD- 4030 | 3.0 |     |                |    |                |                |
| CCD- 4031 | 3.1 |     |                |    |                |                |
| CCD- 4032 | 3.2 | 4   | 22             | 58 | 34             | 16             |
| CCD- 4033 | 3.3 |     |                |    |                |                |
| CCD- 4034 | 3.4 |     |                |    |                |                |
| CCD- 4035 | 3.5 |     |                |    |                |                |
| CCD- 4036 | 3.6 | 5   | 28             | 66 | 36             | 20             |
| CCD- 4037 | 3.7 |     |                |    |                |                |
| CCD- 4038 | 3.8 |     |                |    |                |                |
| CCD- 4039 | 3.9 |     |                |    |                |                |
| CCD- 4040 | 4.0 | 6   | 34             | 72 | 36             | 25             |
| CCD- 4041 | 4.1 |     |                |    |                |                |
| CCD- 4042 | 4.2 |     |                |    |                |                |
| CCD- 4043 | 4.3 |     |                |    |                |                |
| CCD- 4044 | 4.4 | 6   | 34             | 72 | 36             | 25             |
| CCD- 4045 | 4.5 |     |                |    |                |                |
| CCD- 4046 | 4.6 |     |                |    |                |                |
| CCD- 4047 | 4.7 |     |                |    |                |                |
| CCD- 4048 | 4.8 | 6   | 34             | 72 | 36             | 25             |
| CCD- 4049 | 4.9 |     |                |    |                |                |
| CCD- 4050 | 5.0 |     |                |    |                |                |
| CCD- 4051 | 5.1 |     |                |    |                |                |
| CCD- 4052 | 5.2 | 6   | 34             | 72 | 36             | 25             |
| CCD- 4053 | 5.3 |     |                |    |                |                |
| CCD- 4054 | 5.4 |     |                |    |                |                |
| CCD- 4055 | 5.5 |     |                |    |                |                |
| CCD- 4056 | 5.6 | 6   | 34             | 72 | 36             | 25             |
| CCD- 4057 | 5.7 |     |                |    |                |                |
| CCD- 4058 | 5.8 |     |                |    |                |                |
| CCD- 4059 | 5.9 |     |                |    |                |                |
| CCD- 4060 | 6.0 | 6   | 34             | 72 | 36             | 25             |

| EDP No.   | Dø   | dø | L <sub>2</sub> | L   | L <sub>4</sub> | L <sub>s</sub> |
|-----------|------|----|----------------|-----|----------------|----------------|
| CCD- 4061 | 6.1  | 7  | 38             | 76  | 36             | 28             |
| CCD- 4062 | 6.2  |    |                |     |                |                |
| CCD- 4063 | 6.3  |    |                |     |                |                |
| CCD- 4064 | 6.4  |    |                |     |                |                |
| CCD- 4065 | 6.5  |    |                |     |                |                |
| CCD- 4066 | 6.6  |    |                |     |                |                |
| CCD- 4067 | 6.7  |    |                |     |                |                |
| CCD- 4068 | 6.8  |    |                |     |                |                |
| CCD- 4069 | 6.9  | 8  | 44             | 82  | 36             | 32             |
| CCD- 4070 | 7.0  |    |                |     |                |                |
| CCD- 4071 | 7.1  |    |                |     |                |                |
| CCD- 4072 | 7.2  |    |                |     |                |                |
| CCD- 4073 | 7.3  | 8  | 44             | 82  | 36             | 32             |
| CCD- 4074 | 7.4  |    |                |     |                |                |
| CCD- 4075 | 7.5  |    |                |     |                |                |
| CCD- 4076 | 7.6  |    |                |     |                |                |
| CCD- 4077 | 7.7  | 8  | 44             | 82  | 36             | 32             |
| CCD- 4078 | 7.8  |    |                |     |                |                |
| CCD- 4079 | 7.9  |    |                |     |                |                |
| CCD- 4080 | 8.0  |    |                |     |                |                |
| CCD- 4081 | 8.1  | 9  | 50             | 92  | 40             | 38             |
| CCD- 4082 | 8.2  |    |                |     |                |                |
| CCD- 4083 | 8.3  |    |                |     |                |                |
| CCD- 4084 | 8.4  |    |                |     |                |                |
| CCD- 4085 | 8.5  |    |                |     |                |                |
| CCD- 4086 | 8.6  |    |                |     |                |                |
| CCD- 4087 | 8.7  |    |                |     |                |                |
| CCD- 4088 | 8.8  |    |                |     |                |                |
| CCD- 4089 | 8.9  | 10 | 58             | 100 | 40             | 43             |
| CCD- 4090 | 9.0  |    |                |     |                |                |
| CCD- 4091 | 9.1  |    |                |     |                |                |
| CCD- 4092 | 9.2  |    |                |     |                |                |
| CCD- 4093 | 9.3  | 10 | 58             | 100 | 40             | 43             |
| CCD- 4094 | 9.4  |    |                |     |                |                |
| CCD- 4095 | 9.5  |    |                |     |                |                |
| CCD- 4096 | 9.6  |    |                |     |                |                |
| CCD- 4097 | 9.7  | 11 | 60             | 107 | 45             | 45             |
| CCD- 4098 | 9.8  |    |                |     |                |                |
| CCD- 4099 | 9.9  |    |                |     |                |                |
| CCD- 4100 | 10.0 |    |                |     |                |                |
| CCD- 4101 | 10.1 | 11 | 60             | 107 | 45             | 45             |
| CCD- 4102 | 10.2 |    |                |     |                |                |
| CCD- 4103 | 10.3 |    |                |     |                |                |
| CCD- 4104 | 10.4 |    |                |     |                |                |
| CCD- 4105 | 10.5 | 11 | 60             | 107 | 45             | 45             |
| CCD- 4106 | 10.6 |    |                |     |                |                |
| CCD- 4107 | 10.7 |    |                |     |                |                |
| CCD- 4108 | 10.8 |    |                |     |                |                |
| CCD- 4109 | 10.9 | 11 | 60             | 107 | 45             | 45             |
| CCD- 4110 | 11.0 |    |                |     |                |                |

| EDP No.   | Dø   | dø | L <sub>2</sub> | L   | L <sub>4</sub> | L <sub>s</sub> |
|-----------|------|----|----------------|-----|----------------|----------------|
| CCD- 4111 | 11.1 | 12 | 63             | 110 | 45             | 47             |
| CCD- 4112 | 11.2 |    |                |     |                |                |
| CCD- 4113 | 11.3 |    |                |     |                |                |
| CCD- 4114 | 11.4 |    |                |     |                |                |
| CCD- 4115 | 11.5 |    |                |     |                |                |
| CCD- 4116 | 11.6 |    |                |     |                |                |
| CCD- 4117 | 11.7 |    |                |     |                |                |
| CCD- 4118 | 11.8 |    |                |     |                |                |
| CCD- 4119 | 11.9 | 13 | 71             | 118 | 45             | 54             |
| CCD- 4120 | 12.0 |    |                |     |                |                |
| CCD- 4121 | 12.1 |    |                |     |                |                |
| CCD- 4122 | 12.2 |    |                |     |                |                |
| CCD- 4123 | 12.3 | 14 | 77             | 124 | 45             | 58             |
| CCD- 4124 | 12.4 |    |                |     |                |                |
| CCD- 4125 | 12.5 |    |                |     |                |                |
| CCD- 4126 | 12.6 |    |                |     |                |                |
| CCD- 4127 | 12.7 |    |                |     |                |                |
| CCD- 4128 | 12.8 |    |                |     |                |                |
| CCD- 4129 | 12.9 |    |                |     |                |                |
| CCD- 4130 | 13.0 |    |                |     |                |                |
| CCD- 4131 | 13.1 | 15 | 83             | 133 | 48             | 63             |
| CCD- 4132 | 13.2 |    |                |     |                |                |
| CCD- 4133 | 13.3 |    |                |     |                |                |
| CCD- 4134 | 13.4 |    |                |     |                |                |
| CCD- 4135 | 13.5 |    |                |     |                |                |
| CCD- 4136 | 13.6 |    |                |     |                |                |
| CCD- 4137 | 13.7 |    |                |     |                |                |
| CCD- 4138 | 13.8 |    |                |     |                |                |
| CCD- 4139 | 13.9 | 16 | 83             | 133 | 48             | 63             |
| CCD- 4140 | 14.0 |    |                |     |                |                |
| CCD- 4141 | 14.1 |    |                |     |                |                |
| CCD- 4142 | 14.2 |    |                |     |                |                |
| CCD- 4143 | 14.3 | 17 | 93             | 143 | 48             | 71             |
| CCD- 4144 | 14.4 |    |                |     |                |                |
| CCD- 4145 | 14.5 |    |                |     |                |                |
| CCD- 4146 | 14.6 |    |                |     |                |                |
| CCD- 4147 | 14.7 | 18 | 93             | 143 | 48             | 71             |
| CCD- 4148 | 14.8 |    |                |     |                |                |
| CCD- 4149 | 14.9 |    |                |     |                |                |
| CCD- 4150 | 15.0 |    |                |     |                |                |
| CCD- 4155 | 15.5 | 19 | 101            | 153 | 50             | 77             |
| CCD- 4160 | 16.0 |    |                |     |                |                |
| CCD- 4165 | 16.5 |    |                |     |                |                |
| CCD- 4170 | 17.0 |    |                |     |                |                |
| CCD- 4175 | 17.5 | 20 | 101            | 153 | 50             | 77             |
| CCD- 4180 | 18.0 |    |                |     |                |                |
| CCD- 4185 | 18.5 |    |                |     |                |                |
| CCD- 4190 | 19.0 |    |                |     |                |                |
| CCD- 4195 | 19.5 | 20 | 101            | 153 | 50             | 77             |
| CCD- 4200 | 20.0 |    |                |     |                |                |